

LOMEGACLU150

Wall bracket universal



| | Max. load (in daN) |
|------------------|--------------------|
| LOMEGACLU150.100 | 110 |
| LOMEGACLU150.150 | 100 |
| LOMEGACLU150.200 | 90 |
| LOMEGACLU150.250 | 80 |
| LOMEGACLU150.300 | 70 |
| LOMEGACLU150.400 | 50 |
| LOMEGACLU150.500 | 40 |
| LOMEGACLU150.600 | 30 |

| Reference | Finish | ↕ mm | ↔ mm | → ← mm | ↔ mm | kg/stk | 📦 | Unit |
|---------------------------|--------|---------|---------|------------|---------|--------|----|------|
| ZMLOMEGACLU150.100 | DF | 145 | 155 | 1,5 | | 0,300 | 12 | STK |
| ZMLOMEGACLU150.150 | DF | 145 | 195 | 1,5 | | 0,320 | 12 | STK |
| ZMLOMEGACLU150.200 | DF | 145 | 245 | 1,5 | | 0,340 | 12 | STK |
| ZMLOMEGACLU150.250 | DF | 145 | 295 | 1,5 | | 0,450 | 12 | STK |
| ZMLOMEGACLU150.300 | DF | 145 | 345 | 1,5 | | 0,490 | 12 | STK |
| ZMLOMEGACLU150.400 | DF | 145 | 445 | 1,5 | | 0,540 | 6 | STK |
| ZMLOMEGACLU150.500 | DF | 145 | 545 | 1,5 | | 0,710 | 6 | STK |
| ZMLOMEGACLU150.600 | DF | 145 | 645 | 1,5 | | 0,770 | 6 | STK |

Fixing of the cable tray by VM6.20.

Use the VOMEGA to avoid compression of the profile.

Max. load (in daN): uniformly distributed over complete width of cantilever brackets.

Do not use with: VFUL30.065, VFUL35.150, VFU35.150, VFUL 60.050.

Legend finish

- DF = Defender