

LOMEGACLU150

Wall bracket universal



	Max. load (in daN)
LOMEGACLU150.100	110
LOMEGACLU150.150	100
LOMEGACLU150.200	90
LOMEGACLU150.250	80
LOMEGACLU150.300	70
LOMEGACLU150.400	50
LOMEGACLU150.500	40
LOMEGACLU150.600	30

Reference	↑ mm	↔ mm	→ ← mm	↔ mm	kg/stk	📦	Unit
LOMEGACLU150.100	145	155			0,300	12	STK
LOMEGACLU150.150	145	185			0,320	12	STK
LOMEGACLU150.200	145	235			0,340	12	STK
LOMEGACLU150.250	145	285			0,450	12	STK
LOMEGACLU150.300	145	335			0,490	12	STK
LOMEGACLU150.400	145	435			0,540	6	STK
LOMEGACLU150.500	145	535			0,710	6	STK
LOMEGACLU150.600	145	635			0,770	6	STK

Fixing of the cable tray by VM6.20.

Use the VOMEGA to avoid compression of the profile.

Max. load (in daN): uniformly distributed over complete width of cantilever brackets.

Do not use with: VFUL30.065, VFUL35.150, VFU35.150, VFUL 60.050.